

NA-408-1 Cut Sheet



Penn-Union neutral bar, tin-plated aluminum, 8 openings, 6 circuits, mounting hole position 4 and 7, copper or aluminum, AL9CU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NA-408-1>

Technical Specifications

Brand	Penn-Union
Item	Neutral bar
Material	Tin-plated aluminum
Number Of Openings	8
Number Of Circuits	6
Mounting Hole Position	4 and 7
Conductor Size	14-4 AWG stranded copper, 14-8 AWG solid copper, 8-4 AWG stranded aluminum and 12-8 AWG solid aluminum
Conductor Material	Copper or aluminum
Tightening Torque	14-8 AWG 20 in-lb copper or aluminum and 6-4 AWG 31 in-lb copper or aluminum
Dual Rating	AL9CU
Application	Neutral and grounding

Agency Approvals

UL Listed File #	E73393
UL Recognized File #	E12822
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NA-408-1.pdf>
See store item page for other formats.