

NA-409-1 Cut Sheet



Penn-Union neutral bar, tin-plated aluminum, 9 openings, 7 circuits, mounting hole position 3 and 7, copper or aluminum, AL9CU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NA-409-1>

Technical Specifications

| | |
|-------------------------------|--|
| Brand | Penn-Union |
| Item | Neutral bar |
| Material | Tin-plated aluminum |
| Number Of Openings | 9 |
| Number Of Circuits | 7 |
| Mounting Hole Position | 3 and 7 |
| Conductor Size | 14-4 AWG stranded copper, 14-8 AWG solid copper, 8-4 AWG stranded aluminum and 12-8 AWG solid aluminum |
| Conductor Material | Copper or aluminum |
| Tightening Torque | 14-8 AWG 20 in-lb copper or aluminum and 6-4 AWG 31 in-lb copper or aluminum |
| Dual Rating | AL9CU |
| Application | Neutral and grounding |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E73393 |
| UL Recognized File # | E12822 |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NA-409-1.pdf>
See store item page for other formats.