

NA-410-5 Cut Sheet



Penn-Union neutral bar, tin-plated aluminum, 11 openings, 9 circuits, mounting hole position 1 and 11, copper or aluminum, AL9CU. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NA-410-5>

Technical Specifications

Brand	Penn-Union
Item	Neutral bar
Material	Tin-plated aluminum
Number Of Openings	11
Number Of Circuits	9
Mounting Hole Position	1 and 11
Conductor Size	14-4 AWG stranded copper, 14-8 AWG solid copper, 8-4 AWG stranded aluminum and 12-8 AWG solid aluminum

Conductor Material	Copper or aluminum
Tightening Torque	14-8 AWG 20 in-lb copper or aluminum and 6-4 AWG 31 in-lb copper or aluminum
Dual Rating	AL9CU
Application	Neutral and grounding
Quantity per Pack	5

Agency Approvals

UL Listed File #	E12822, E73393
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NA-410-5.pdf>
See store item page for other formats.