

NA-416-5 Cut Sheet

Penn-Union neutral bar, tin-plated aluminum, 12 openings, 10 circuits, mounting hole position 3 and 11, aluminum, AL9. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NA-416-5>

Technical Specifications

Brand	Penn-Union
Item	Neutral bar
Material	Tin-plated aluminum
Number Of Openings	12
Number Of Circuits	10
Mounting Hole Position	3 and 11
Conductor Size	8–2 AWG stranded aluminum and 12–8 AWG solid aluminum

Conductor Material	Aluminum
Tightening Torque	12–10 AWG 35 in-lb aluminum, 8 AWG 40 in-lb aluminum, 6–4 AWG 45 in-lb aluminum and 2 AWG 50 in-lb aluminum
Dual Rating	AL9
Application	Neutral and grounding
Quantity per Pack	5

Agency Approvals

UL Listed File #	E12822, E73393
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NA-416-5.pdf>
See store item page for other formats.