

ND5015-070-61 Cut Sheet



Dold AC/DC current transformer, solid core, 70mm diameter sensing window, +/- 3% accuracy. For use with Dold RN5883-011-24-80V or RN5883-011-80-230V residual current monitors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ND5015-070-61>

Technical Specifications

Brand	Dold
Item	Transformer
Transformer Type	Current
Voltage Type	AC/DC
Body Type	Solid core
Sensing Window	70mm diameter
Accuracy	+/- 3%
Connector Type	Push-in terminals
Mounting	Panel or 35mm DIN rail
For Use With	Dold RN5883-011-24-80V or RN5883-011-80-230V residual current monitors

Agency Approvals

UL Listed File #	None
UL Recognized File #	E249129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ND5015-070-61.pdf>
See store item page for other formats.