

NE-M1ANB-M Cut Sheet



Patlite NE-A series integrated LED audible-visual signal beacon, 88 dB at 1m, continuous/intermittent tone(s), continuous or flashing (500ms), multi-color, 56mm, 12-24 VDC, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NE-M1ANB-M>

Technical Specifications

Brand	Patlite
Item	Audible-visual signal beacon
Series	NE-A
Bulb Type	Integrated LED
Operator Size	56mm
Operator Color	White
Light Color(s)	Red/amber/green/blue/white/cyan/purple
Light Function	Continuous or flashing (500ms)
Housing Material	Polycarbonate

Material	ABS/polycarbonate
Loudness Decibel	88 dB at 1m
Tone Frequency	2.5 kHz
Tone Type	Continuous/intermittent
Touch to Acknowledge	No
Number of Alarms	2
Voltage Rating	12-24 VDC
Mounting	Direct
IP Rating	IP65

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NE-M1ANB-M.pdf>
See store item page for other formats.