

# NFLT-020-L60 Cut Sheet



ProSense hydrostatic submersible level transmitter, 0 to 20 psig (46.1ft of water column) sensing range, 4-20 mA, 1.26in diameter housing, shielded and vented 60ft cable, hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NFLT-020-L60>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Submersible level transmitter
<b>Sensor Type</b>	Hydrostatic
<b>Sensing Range</b>	0 to 20 psig (46.1ft of water column)
<b>Output</b>	4-20 mA
<b>Operating Voltage</b>	11-30 VDC
<b>Housing Size</b>	1.26in diameter
<b>Housing Material</b>	Stainless steel
<b>Electrical Connection</b>	Shielded and vented 60ft cable
<b>Jacket Material</b>	Polyethylene
<b>Application</b>	Hazardous location rated

## Agency Approvals

<b>UL Listed File #</b>	E537209
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/NFLT-020-L60.pdf>  
See store item page for other formats.