

NK-T-21-1ST8-2 Cut Sheet



Schmersal selector switch, IP65, IP67, IP69 and IP69K, 22mm, 2-position, momentary, (2) N.O. contact(s), plastic base, plastic bezel, Operator: blue, joystick, 25mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NK-T-21-1ST8-2>

Technical Specifications

Brand	Schmersal
Item	Selector switch
Barrel Size	22mm
IP Rating	IP65, IP67, IP69 and IP69K
Number Of Positions	2
Action	Momentary
Contact Type	(2) N.O.
Base Material	Plastic

Bezel Material	Plastic
Operator Color	Blue
Operator Type	Joystick
Operator Size	25mm
Operator Shape	Round
Operator Material	Plastic
Connection	(1) 8-pin M12 quick-disconnect
Application	Suitable for food and beverage applications

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/NK-T-21-1ST8-2.pdf>
See store item page for other formats.