

# NK-T-22-2ST8-2 Cut Sheet



Schmersal selector switch, IP65, IP67, IP69 and IP69K, 22mm, 2-position, momentary, (4) N.O. contact(s), plastic base, plastic bezel, Operator: blue, joystick, 25mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NK-T-22-2ST8-2>

## Technical Specifications

<b>Brand</b>	Schmersal
<b>Item</b>	Selector switch
<b>Barrel Size</b>	22mm
<b>IP Rating</b>	IP65, IP67, IP69 and IP69K
<b>Number Of Positions</b>	2
<b>Action</b>	Momentary
<b>Contact Type</b>	(4) N.O.
<b>Base Material</b>	Plastic

<b>Bezel Material</b>	Plastic
<b>Operator Color</b>	Blue
<b>Operator Type</b>	Joystick
<b>Operator Size</b>	25mm
<b>Operator Shape</b>	Round
<b>Operator Material</b>	Plastic
<b>Connection</b>	(2) 8-pin M12 quick-disconnect
<b>Application</b>	Suitable for food and beverage applications

## Agency Approvals

<b>UL Listed File #</b>	E57648
<b>UL Recognized File #</b>	NONE
<b>UL Hazardous File #</b>	NONE
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	NONE
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/NK-T-22-2ST8-2.pdf>  
See store item page for other formats.