
NKE-4/7.33 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



BLOCK NKE series line reactor, 120/230 VAC, 1-phase, 4A, 1/6 hp at 120/230 VAC, open frame, 4% impedance, input side only. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/NKE-4/7.33

Technical Specifications

Brand	BLOCK
Item	Line reactor
Series	NKE
Maximum Voltage	690 VAC
Design Voltage Rating	120/230 VAC
Number of Phases	1
Amperage Rating	4A
Horsepower by Voltage	1/6 hp at 120/230 VAC
Enclosure Type	Open frame
Impedance	4%
Inductance	7.33
Orientation	Input side only
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	E103521
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/NKE-4_7.33.pdf
See store item page for other formats.