
# NKE-6/4.88 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



BLOCK NKE series line reactor, 120/230 VAC, 1-phase, 6A, 1/4 hp at 120/230 VAC, open frame, 4% impedance, input side only. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/NKE-6/4.88

## Technical Specifications

| | |
|---|---|
| **Brand** | BLOCK |
| **Item** | Line reactor |
| **Series** | NKE |
| **Maximum Voltage** | 690 VAC |
| **Design Voltage Rating** | 120/230 VAC |
| **Number of Phases** | 1 |
| **Amperage Rating** | 6A |
| **Horsepower by Voltage** | 1/4 hp at 120/230 VAC |
| **Enclosure Type** | Open frame |
| **Impedance** | 4% |
| **Inductance** | 4.88 |
| **Orientation** | Input side only |
| **For Use With** | Multiple AC drives |

## Agency Approvals

| | |
|---|---|
| **UL Listed File #** | None |
| **UL Recognized File #** | E103521 |
| **UL Hazardous File #** | None |
| **CE** | View CE declarations |
| **CSA File #** | None |
| **RoHS Status** | Yes (See CE Doc) |
| **EU REACH** | View EU REACH document |

## Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/NKE-6_4.88.pdf
See store item page for other formats.