

NLBHB-12-38N Cut Sheet



HydroMode threaded fitting, hose barb, lead-free brass body, lead-free brass threads, (1) 1/2in hose to (1) 3/8in male NPT connection(s). Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NLBHB-12-38N>

Technical Specifications

Brand	HydroMode
Item	Fitting
Fitting Connection Type	Threaded
Fitting Type	Hose barb
Body Material	Lead-free brass
Thread Material	Lead-free brass
Connection	(1) 1/2in hose and (1) 3/8in male NPT
Operating Pressure	800 psi
Quantity per Pack	3

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/NLBHB-12-38N.pdf>
See store item page for other formats.