

NLBHB-14-18N Cut Sheet



HydroMode threaded fitting, hose barb, lead-free brass body, lead-free brass threads, (1) 1/4in hose to (1) 1/8in male NPT connection(s). Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NLBHB-14-18N>

Technical Specifications

| | |
|-----------------------------|--------------------------------------|
| Brand | HydroMode |
| Item | Threaded Fitting |
| Fitting Type | Hose barb |
| Body Material | Lead-free brass |
| Thread Material | Lead-free brass |
| Port Connection Info | (1) 1/4in hose to (1) 1/8in male NPT |
| Operating Pressure | 800 psi |
| Quantity per Pack | 3 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |