

# NLBHB-516-18N Cut Sheet



HydroMode threaded fitting, hose barb, lead-free brass body, lead-free brass threads, (1) 5/16in hose to (1) 1/8in male NPT connection(s). Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NLBHB-516-18N>

## Technical Specifications

|                             |                                       |
|-----------------------------|---------------------------------------|
| <b>Brand</b>                | HydroMode                             |
| <b>Item</b>                 | Threaded Fitting                      |
| <b>Fitting Type</b>         | Hose barb                             |
| <b>Body Material</b>        | Lead-free brass                       |
| <b>Thread Material</b>      | Lead-free brass                       |
| <b>Port Connection Info</b> | (1) 5/16in hose to (1) 1/8in male NPT |
| <b>Operating Pressure</b>   | 800 psi                               |
| <b>Quantity per Pack</b>    | 3                                     |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |