

# NM-12-100 Cut Sheet



Electri-Flex Liquatite liquid-tight flexible non-metallic conduit, embedded spiral rigid PVC, PVC wall, 3/4in trade size, gray, UL-1660 Listed, 100ft/30.4m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NM-12-100>

## Technical Specifications

<b>Brand</b>	Electri-Flex	<b>Color</b>	Gray
<b>Series</b>	Liquatite	<b>Coil Length</b>	100ft/30.4m
<b>Item</b>	Conduit	<b>UL Rating</b>	UL-1660 Listed
<b>Conduit Type</b>	Liquid-tight flexible non-metallic conduit (LFNC)	<b>Operating Temperature</b>	-4 deg F to 176 deg F (-20 deg C to 80 deg C)
<b>Liquid-tight</b>	Yes	<b>UV Resistant</b>	Yes
<b>Inner Core Material</b>	Embedded spiral rigid PVC	<b>Applicable Standards</b>	<ul style="list-style-type: none"><li>• ANSI/UL-1660 Type B</li><li>• CSA C22.2 No 227.2 Type B</li></ul>
<b>Outer Material</b>	PVC wall	<b>Application</b>	General purpose
<b>Trade Size</b>	3/4in		

## Agency Approvals

<b>UL Listed File #</b>	E79308
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	LL230485
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>