

NM-13-50 Cut Sheet



Electri-Flex Liquatite liquid-tight flexible non-metallic conduit, embedded spiral rigid PVC, PVC wall, 1in trade size, gray, UL-1660 Listed, 50ft/15.2m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NM-13-50>

Technical Specifications

Brand	Electri-Flex
Series	Liquatite
Item	Conduit
Conduit Type	Liquid-tight flexible non-metallic conduit (LFNC)
Liquid-tight	Yes
Inner Core Material	Embedded spiral rigid PVC
Outer Material	PVC wall
Trade Size	1in

Color	Gray
Coil Length	50ft/15.2m
UL Rating	UL-1660 Listed
Operating Temperature	-4 deg F to 176 deg F (-20 deg C to 80 deg C)
UV Resistant	Yes
Applicable Standards	<ul style="list-style-type: none">• ANSI/UL-1660 Type B• CSA C22.2 No 227.2 Type B
Application	General purpose

Agency Approvals

UL Listed File #	E79308
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL230485
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement