

NP2424SS Cut Sheet



Wiegmann subpanel, 304 stainless steel. For use with 24x24/24x25 (HxW) B2424xxCH, N122424xx, N4242408, RHC242408, SDN122425xxPL, SN4242508, SSN42424xxx, SSN4X242508x and WA242408FM enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NP2424SS>

Technical Specifications

Brand	Wiegmann
Item	Subpanel
Height	21in
Width	21in
Thickness	12 gauge
Material	304 stainless steel
Perforations accept self-tapping screws for mounting lightweight components	No
For Use With	24x24/24x25 (HxW) B2424xxCH, N122424xx, N4242408, RHC242408, SDN122425xxPL, SN4242508, SSN42424xxx, SSN4X242508x and WA242408FM enclosures

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/NP2424SS.pdf>
See store item page for other formats.