

NS211YF24FPDG4 Cut Sheet



GC Valves potable water solenoid valve, 2-port (2-way), 2-position, N.C., Nylon 6 body, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), Cv=4.3, 24 VAC operating voltage, 8W.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NS211YF24FPDG4>

Technical Specifications

| | |
|----------------------------|-------------------------------|
| Brand | GC Valves |
| Item | Valve |
| Working Fluid | Potable water |
| Valve Type | Solenoid process |
| Port Quantity | 2-port (2-way) |
| Number Of Positions | 2 |
| Valve Configuration | N.C. |
| Action | Single solenoid spring return |
| Body Material | Nylon 6 |

| | |
|-----------------------------------|----------------------------|
| Inlet Port | 1/2in female NPT |
| Outlet Port | 1/2in female NPT |
| Flow Coefficient | 4.3 |
| Minimum Operating Pressure | 4 psi |
| Maximum Operating Pressure | 150 psi |
| Operating Voltage | 24 VAC |
| Power Rating | 8W |
| Electrical Connection | 18mm DIN style wiring plug |
| Form Factor | Standard |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | MH17998 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 069111_0_000 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | NSF Listing |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/NS211YF24FPDG4.pdf>
See store item page for other formats.