

# NVA1000-ADC Cut Sheet



Winters manual isolation and throttling needle valve, straight body soft seat, single handle, stainless steel body, 1/4in male NPT inlet(s), 1/4in female NPT outlet(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NVA1000-ADC>

## Technical Specifications

Brand	Winters
Item	Needle valve
Valve Type	Manual isolation and throttling
Form Factor	Straight body soft seat
Operator Type	Single handle
Body Material	Stainless steel
Inlet Port	1/4in male NPT
Outlet Port	1/4in female NPT
Operating Pressure	6,000 psi @ 212°F
Operating Temperature	32°F to 977°F (0°C to 525°C)

## Agency Approvals

CE	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/NVA1000-ADC.pdf>  
See store item page for other formats.