

NW302410HWT Cut Sheet



Stahlin N series enclosure, NEMA 1/3/3R/4X/12, 30 x 24 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (5) twist-lock latches, padlock hasp and staple, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NW302410HWT>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Stahlin |
| Item | Enclosure |
| Series | N |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 1/3/3R/4X/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 30 x 24 x 10in (HxWxD) |
| Enclosure Height | 33.41in |
| Enclosure Width | 26.32in |
| Enclosure Depth | 11.95in |
| Mounting | Wall |
| Integral Mounting Feet | Yes |

| | |
|----------------------------------|---------------------------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Fiberglass reinforced polyester |
| Color | Gray |
| Cover Type | Single-door |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | (5) twist-lock latches |
| Padlock Attachment Type | Padlock hasp and staple |
| Shelf | No |
| Window Material | SAR acrylic |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | | |
|-----------------------------|--|---------|
| UL Listed File # | E64358 | E362920 |
| UL Recognized File # | E333478 | |
| UL Hazardous File # | None | |
| CE | View CE declarations | |
| CSA File # | LR069014 | |
| RoHS Status | Yes (See CE Doc) | |
| EU REACH | View EU REACH document | |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NW302410HWT.pdf>
See store item page for other formats.