

NWTS321WS Cut Sheet



Schmersal selector switch, IP67 and IP69K, 22mm, 3-position, spring return to center from left, maintained right, operator only, plastic base, plastic bezel, Operator: white, knob, 44mm, round, plastic. Requires contact blocks.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NWTS321WS>

Technical Specifications

Brand	Schmersal
Item	Selector switch
Barrel Size	22mm
IP Rating	IP67 and IP69K
Number Of Positions	3
Action	Spring return to center from left, maintained right
Contact Type	Operator only
Base Material	Plastic

Bezel Material	Plastic
Operator Color	White
Operator Type	Knob
Operator Size	44mm
Operator Shape	Round
Operator Material	Plastic
Operator Legend	Arrow and line
Requires	Contact blocks

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/NWTS321WS.pdf>
See store item page for other formats.