

# O-S1-S-250-40 Cut Sheet



di-soric lens, 25mm focal length, fixed f/4.0 aperture, S-mount.  
For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/O-S1-S-250-40>

## Technical Specifications

|                     |             |
|---------------------|-------------|
| Brand               | di-soric    |
| Item                | Lens        |
| Focal Length        | 25mm        |
| Aperture            | Fixed f/4.0 |
| Lens Type           | Standard    |
| Lens Mount          | S-mount     |
| Maximum Sensor Size | 1/2in       |
| Diameter            | 14mm        |
| Length              | 20.1mm      |
| Filter Thread Size  | M12 x 0.5   |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/O-S1-S-250-40.pdf>  
See store item page for other formats.