

OCH.2.2123 Cut Sheet



SapiSelco mounting head cable tie, 7.87in length, 0.18in width, 48.5lb tensile strength, 2.01in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OCH.2.2123>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Mounting head
Length	7.87in
Width	0.18in
Tensile Strength	48.5lb
Maximum Bundle Diameter	2.01in
Color	Natural
Material	Nylon
Temperature Rating	+23 to +185 deg F
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document