

OP-2CBL-1 Cut Sheet



AutomationDirect communication cable, 15-pin D-shell male to 15-pin D-sub HD15 male, shielded, 2m/6.6ft cable length. For use with any OP600 or OP1000 series OptiMate unit and a DL06, or the bottom port of a D2-250(-1), D2-260 or D2-262 (bottom port) CPU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OP-2CBL-1>

Technical Specifications

| | |
|--------------|---|
| Brand | AutomationDirect |
| Item | Communication Cable |
| Connection 1 | 15-pin D-shell male |
| Connection 2 | 15-pin D-sub HD15 male |
| Shielded | Yes |
| Cable Length | 2m/6.6ft |
| For Use With | Any OP600 or OP1000 series OptiMate unit and a DL06, or the bottom port of a D2-250(-1), D2-260 or D2-262 (bottom port) CPU |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |