

OPT2010 Cut Sheet



Wenglor photoelectric sensor, square, polycarbonate, diffuse with background suppression, 0-3m sensing distance, complementary light-on/dark-on, PNP, teach-in button, 1 kHz switching frequency, 5-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2010>

Technical Specifications

Brand	Wenglor
Item	Photoelectric sensor
Shape	Square
Housing Size	50 x 50 x 20mm
IP Rating	IP68
Housing Material	Polycarbonate
Sensing Method	Diffuse with background suppression
Sensing Technology	Time of Flight technology
Operating Voltage	10-30 VDC
Switching Output	PNP
Sensing Distance	0-3m
Sensitivity	Teach-in button
Operation Mode	Complementary light-on/dark-on
Switching Frequency	1 kHz
Light emission	Class 1 laser
User Interface	Pushbutton user interface
Connection	5-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E189727
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document