

OPT2028 Cut Sheet



Wenglor contrast sensor, square, diffuse, white, 30-40mm sensing distance, selectable light-on/dark-on, PNP, teach-in button, 25 kHz switching frequency, plastic housing, 8-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2028>

Technical Specifications

Brand	Wenglor
Item	Contrast sensor
Shape	Square
Housing Size	50 x 50 x 20mm
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Diffuse
Sensor Type	Print mark
Operating Voltage	10-30 VDC

Switching Output	PNP
Sensing Distance	30-40mm
Sensitivity	Teach-in button
Operation Mode	Selectable light-on/dark-on
Switching Frequency	25 kHz
Light Emission (NP)	White
Connection	8-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E189727
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/OPT2028.pdf>
See store item page for other formats.