

# OPT2040 Cut Sheet



Wenglor fiber amplifier, rectangular, 1-channel, pushbutton user interface, NPN/PNP, programmable switching, impulse or time delay outputs, 10-30 VDC operating voltage, 4-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2040>

## Technical Specifications

Brand	Wenglor
Item	Fiber amplifier
Shape	Rectangular
Number Of Channels	1
User Interface	Pushbutton user interface
Switching Output	NPN/PNP
Operation Mode	Programmable switching, impulse or time delay outputs
Sensitivity Adjustment	Teach-in sensitivity adjustment
IO-Link Compatible	No

Operating Voltage	10-30 VDC
Housing Material	Plastic
Housing Size	12 x 30 x 68mm
Connection	4-pin M8 quick-disconnect
Mounting	35mm DIN rail
IP Rating	IP65
Switching Frequency	2 kHz
For Use With	Plastic cuttable or glass fibers
Additional Information	Purchase fiber and connection cables separately

## Agency Approvals

UL Listed File #	E189727
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/OPT2040.pdf>  
See store item page for other formats.