

OPT2052 Cut Sheet

Wenglor optical fiber, plastic, cuttable, diffuse, coaxial fibers, 3mm diameter head, stainless steel, polyethylene jacket, 60mm sensing distance, 2m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2052>

Technical Specifications

Brand	Wenglor
Item	Optical fiber
Fiber Type	Plastic
Cuttable	Yes
Sensing Method	Diffuse
Fiber Distribution	Coaxial fibers
Head Size	3mm diameter
Head Material	Stainless steel
Jacket Material	Polyethylene jacket
Maximum Sensing Distance	60mm
Length	2m
Includes	Fiber cutter

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document