

# OPT2054 Cut Sheet



Wenglor optical fiber, plastic, cuttable, diffuse, parallel fibers, M6 head, nickel-plated brass, polyethylene jacket, 160mm sensing distance, 2m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2054>

## Technical Specifications

<b>Brand</b>	Wenglor
<b>Item</b>	Optical fiber
<b>Fiber Type</b>	Plastic
<b>Cuttable</b>	Yes
<b>Sensing Method</b>	Diffuse
<b>Fiber Distribution</b>	Parallel fibers
<b>Head Size</b>	M6
<b>Head Material</b>	Nickel-plated brass
<b>Jacket Material</b>	Polyethylene jacket
<b>Maximum Sensing Distance</b>	160mm
<b>Length</b>	2m
<b>Includes</b>	Fiber cutter and mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>