

OPT2055 Cut Sheet

Wenglor optical fiber, plastic, cuttable, diffuse, parallel fibers, M6 head, nickel-plated brass, polyethylene jacket, 60mm sensing distance, 2m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2055>



Technical Specifications

Brand	Wenglor
Item	Optical fiber
Fiber Type	Plastic
Cuttable	Yes
Sensing Method	Diffuse
Fiber Distribution	Parallel fibers
Head Size	M6
Head Material	Nickel-plated brass
Jacket Material	Polyethylene jacket
Maximum Sensing Distance	60mm
Length	2m
Includes	Fiber cutter and mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document