

OPT2060 Cut Sheet



Wenglor optical fiber, plastic, cuttable, diffuse, parallel fibers, 12mm flat head, aluminum, 90-degree, polyethylene jacket, 50mm sensing distance, 2m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2060>

Technical Specifications

Brand	Wenglor
Item	Optical fiber
Fiber Type	Plastic
Cuttable	Yes
Sensing Method	Diffuse
Fiber Distribution	Parallel fibers
Head Size	12mm flat

Head Material	Aluminum
Head Angle	90-degree
Jacket Material	Polyethylene jacket
Maximum Sensing Distance	50mm
Length	2m
Includes	Fiber cutter

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/OPT2060.pdf>
See store item page for other formats.