

# OPT2061 Cut Sheet



Wenglor optical fiber, plastic, cuttable, diffuse, parallel fibers, M4 head, stainless steel, 90-degree, polyethylene jacket, 70mm sensing distance, 2m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2061>

## Technical Specifications

Brand	Wenglor
Item	Optical fiber
Fiber Type	Plastic
Cuttable	Yes
Sensing Method	Diffuse
Fiber Distribution	Parallel fibers
Head Size	M4

Head Material	Stainless steel
Head Angle	90-degree
Jacket Material	Polyethylene jacket
Maximum Sensing Distance	70mm
Length	2m
Includes	Fiber cutter and mounting hardware

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/OPT2061.pdf>  
See store item page for other formats.