

OPT2062 Cut Sheet

Wenglor optical fiber, plastic, cuttable, diffuse, parallel fibers, 5mm diameter head, stainless steel, 90-degree, polyethylene jacket, 50mm sensing distance, 2m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2062>



Technical Specifications

| | |
|---------------------------------|---------------------|
| Brand | Wenglor |
| Item | Optical fiber |
| Fiber Type | Plastic |
| Cuttable | Yes |
| Sensing Method | Diffuse |
| Fiber Distribution | Parallel fibers |
| Head Size | 5mm diameter |
| Head Material | Stainless steel |
| Head Angle | 90-degree |
| Jacket Material | Polyethylene jacket |
| Maximum Sensing Distance | 50mm |
| Length | 2m |
| Includes | Fiber cutter |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |