

OPT2064 Cut Sheet



Wenglor optical fiber, plastic, cuttable, through-beam, parallel fibers, M3 head, stainless steel, polyethylene jacket, 160mm sensing distance, 2m length. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2064>

Technical Specifications

Brand	Wenglor
Item	Optical fiber
Fiber Type	Plastic
Cuttable	Yes
Sensing Method	Through-beam
Fiber Distribution	Parallel fibers
Head Size	M3

Head Material	Stainless steel
Jacket Material	Polyethylene jacket
Maximum Sensing Distance	160mm
Length	2m
Quantity per Pack	2
Includes	Fiber cutter and mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/OPT2064.pdf>
See store item page for other formats.