

OPT2065 Cut Sheet



Wenglor optical fiber, plastic, cuttable, through-beam, parallel fibers, M3 head, nickel-plated brass, polyethylene jacket, 400mm sensing distance, 2m length. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2065>

Technical Specifications

Brand	Wenglor
Item	Optical fiber
Fiber Type	Plastic
Cuttable	Yes
Sensing Method	Through-beam
Fiber Distribution	Parallel fibers
Head Size	M3

Head Material	Nickel-plated brass
Jacket Material	Polyethylene jacket
Maximum Sensing Distance	400mm
Length	2m
Quantity per Pack	2
Includes	Fiber cutter and mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/OPT2065.pdf>
See store item page for other formats.