

# OPT2082 Cut Sheet

Wenglor optical fiber, glass, diffuse, separated bundles, M6 head, aluminum, nickel plated brass jacket, 160mm sensing distance, 1m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2082>



## Technical Specifications

<b>Brand</b>	Wenglor
<b>Item</b>	Optical fiber
<b>Fiber Type</b>	Glass
<b>Cutttable</b>	No
<b>Sensing Method</b>	Diffuse
<b>Fiber Distribution</b>	Separated bundles
<b>Head Size</b>	M6
<b>Head Material</b>	Aluminum
<b>Jacket Material</b>	Nickel plated brass jacket
<b>Maximum Sensing Distance</b>	160mm
<b>Length</b>	1m

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>