

OPT2087 Cut Sheet



Wenglor optical fiber, glass, through-beam, statistic mixture, M18 head, aluminum, nickel plated brass jacket, 600mm sensing distance, 1m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2087>

Technical Specifications

Brand	Wenglor
Item	Optical fiber
Fiber Type	Glass
Cuttable	No
Sensing Method	Through-beam
Fiber Distribution	Statistic mixture
Head Size	M18
Head Material	Aluminum
Jacket Material	Nickel plated brass jacket
Maximum Sensing Distance	600mm
Length	1m

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document