

OPT2089 Cut Sheet



Wenglor optical fiber, glass, diffuse, statistic mixture, M18 head, aluminum, nickel plated brass jacket, 18mm sensing distance, 1m length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2089>

Technical Specifications

Brand	Wenglor
Item	Optical fiber
Fiber Type	Glass
Cuttable	No
Sensing Method	Diffuse
Fiber Distribution	Statistic mixture
Head Size	M18
Head Material	Aluminum
Jacket Material	Nickel plated brass jacket
Maximum Sensing Distance	18mm
Length	1m

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document