

OPT2132 Cut Sheet



Wenglor photoelectric sensor, square, plastic housing, through-beam emitter, visible red light emission, 0-20m sensing distance, 10-30 VDC operating voltage, 3-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2132>

Technical Specifications

Brand	Wenglor
Item	Photoelectric sensor
Shape	Square
Housing Size	50 x 50 x 20mm
IP Rating	IP67 IP68
Housing Material	Plastic
Sensing Method	Through-beam emitter
Operating Voltage	10-30 VDC
Number of Wires	3
Sensing Distance	0-20m
Light emission	Visible red
IO-Link Compatible	No
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E189727
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document