

OPT2169 Cut Sheet



Wenglor photoelectric sensor, rectangular, plastic, diffuse with background suppression, 30-150mm sensing distance, complementary light-on/dark-on, NPN, potentiometer, 1000 Hz switching frequency, 4-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2169>

Technical Specifications

Brand	Wenglor
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	32 x 16 x 12mm
IP Rating	IP67 IP68
Housing Material	Plastic
Sensing Method	Diffuse with background suppression
Sensing Technology	Shiny object detection
Operating Voltage	10-30 VDC
Number of Wires	4
Switching Output	NPN
Sensing Distance	30-150mm
Sensitivity	Potentiometer

Operation Mode	Complementary light-on/dark-on
Switching Frequency	1000 Hz
Light Emission	Blue
IO-Link Compatible	Yes
Connection	4-pin M8 quick-disconnect
Communication Port and Connection Type(s)	(1) 4-pin M8 (IO-Link) port(s)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.1
Standard I/O Mode Supported	Yes
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E189727
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/OPT2169.pdf>
See store item page for other formats.