

P1-01DC Cut Sheet



Productivity1000 DC power supply, 12-24 VDC nominal input. External power supply optional. For applications not exceeding (8) P1000 modules.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-01DC>

Technical Specifications

Brand	Productivity1000
Item	Power supply
Voltage Type	DC
Nominal Input Voltage	12-24 VDC
Programming Software	Productivity Suite programming software v3.5 or later
Additional Information	External power supply optional. For applications not exceeding (8) P1000 modules

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P1-01DC.pdf>
See store item page for other formats.