

P1-04NTC Cut Sheet



Productivity1000 temperature input module, thermistor, 4-channel, 16-bit resolution, input thermistor type(s): 2252, 10K-AN Type 3, 10K-CP Type 2, 5K, 3K and 1.8K ohm. (1) P1-10RTB screw terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-04NTC>

Technical Specifications

Brand	Productivity1000
Item	Input module
I/O Module Type	Temperature
Input Signal Type(s)	Thermistor
Number Of Channels	4
Input Thermistor Signal Types	2252, 10K-AN Type 3, 10K-CP Type 2, 5K, 3K and 1.8K
Input Resolution	16-bit
Includes	(1) P1-10RTB screw terminal block
Programming Software	Productivity Suite programming software v3.0 or later
Additional Information	Optional P1-10RTB-1 spring clamp terminal block sold separately. Pre-wired ZIPLinks not available for temperature modules

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document