

# P1-08ADL-2 Cut Sheet



Productivity1000 analog input module, 8-channel, voltage, 13-bit, input voltage signal range(s) of 0-10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-08ADL-2>

## Technical Specifications

|   |   |
|---|---|
| <b>Brand</b>                                | Productivity1000  |
| <b>Item</b>                                 | Input module  |
| <b>I/O Module Type</b>                      | Analog  |
| <b>Number Of Input Channels</b>             | 8   |
| <b>Input Signal Type(s)</b>                 | Voltage   |
| <b>Isolated Channels</b>                    | No  |
| <b>Number of Non-Isolated Input Commons</b> | 1   |
| <b>Input Resolution</b>                     | 13-bit  |
| <b>Input Voltage Signal Range</b>           | 0-10 VDC  |
| <b>External Power Requirement</b>           | 24 VDC  |
| <b>Requires</b>                             | P1-10RTB or P1-10RTB-1 removable terminal block or ZIPLink pre-wired cables |
| <b>Programming Software</b>                 | Productivity Suite programming software v3.5 or later                       |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E139594                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |