


P1-08DAL-2 Cut Sheet



Productivity1000 analog output module, 8-channel, voltage, 12-bit, output voltage signal range(s) of 0-10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-08DAL-2>

Technical Specifications

Brand	Productivity1000
Item	Output module
I/O Module Type	Analog
Number Of Output Channels	8
Output Signal Type	Voltage
Isolated Channels	No
Number of Non-Isolated Output Commons	1
Output Resolution	12-bit
Output Voltage Signal Range	0-10 VDC
External Power Requirement	24 VDC
Requires	P1-10RTB or P1-10RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v3.5 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document