

# P1-08TA Cut Sheet



Productivity1000 discrete output module, 8-point, 120-240 VAC, 2 isolated common(s), 4 point(s) per common, 0.5A/point, 4A/common. Requires P1-10RTB or P1-10RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-08TA>

## Technical Specifications

<b>Brand</b>	Productivity1000
<b>Item</b>	Output module
<b>I/O Module Type</b>	Discrete
<b>Number of Output Points</b>	8
<b>Nominal Output Voltage</b>	120-240 VAC
<b>Number of Isolated Output Commons</b>	2
<b>Number of Points per Common</b>	4
<b>Load Current</b>	0.5A/point, 4A/common @ 55 deg C; 0.3A/point, 2.4A/common @ 60 deg C
<b>Fuse Type</b>	External fusing 8A max (user supplied)
<b>Requires</b>	P1-10RTB or P1-10RTB-1 removable terminal block or ZIPLink pre-wired cables
<b>Programming Software</b>	Productivity Suite programming software v3.3 or later
<b>Additional Information</b>	External jumper required for non-isolated 240 VAC applications

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>