

# P1-RX Cut Sheet



Productivity1000 remote I/O module, 1 port, (1) Ethernet (RJ45) port(s). For use with P1-550, P2-550 and P2-622 CPUs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P1-RX>

## Technical Specifications

Brand	Productivity1000
Item	Remote I/O module
Number of Ports	1
Buffered Ports	No
Communication Port and Connection Type(s)	(1) Ethernet (RJ45)
Port Protocol(s)	Ethernet remote I/O
Port Speed(s)	10/100 Mbps
External Power Requirement	24 VDC
For Use With	P1-550, P2-550 and P2-622 CPUs
Programming Software	Productivity Suite programming software v3.10 or later
Additional Information	Supports up to (8) Productivity1000 I/O modules

## Agency Approvals

UL Listed File #	139594
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/P1-RX.pdf>  
See store item page for other formats.