

P2-04AD Cut Sheet



Productivity2000 analog input module, 4-channel, current/voltage, 16-bit, input current signal range(s) of 0-20 mA, input voltage signal range(s) of 0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-04AD>

Technical Specifications

Brand	Productivity2000
Item	Input module
I/O Module Type	Analog
Number Of Input Channels	4
Input Signal Type(s)	Current/voltage
Analog Input Type	Sinking
Isolated Channels	No
Number of Non-Isolated Input Commons	4
Input Resolution	16-bit
Input Current Signal Range	0-20 mA
Input Voltage Signal Range	0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC
Display Type	4 x 10 character OLED display
External Power Requirement	24 VDC
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v2.0 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document