

P2-04DAL-2 Cut Sheet



Productivity2000 analog output module, 4-channel, voltage, 12-bit, external 24 VDC required. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-04DAL-2>

Technical Specifications

Brand	Productivity2000
Item	Output module
I/O Module Type	Analog
Number Of Output Channels	4
Output Signal Type	Voltage
Isolated Channels	No
Number of Non-Isolated Output Commons	8

Output Resolution	12-bit
Output Voltage Signal Range	0-10 VDC
External Power Requirement	24 VDC
Requires	P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables
Programming Software	Productivity Suite programming software v2.3 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	ABS Certification Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/P2-04DAL-2.pdf>
See store item page for other formats.