

P2-06TRS Cut Sheet



Productivity2000 relay output module, 6-point, 5-30 VDC/5-264 VAC, (5) Form A, (1) Form C, 6 isolated common(s), 1 point(s) per common, 7A/point. Requires P2-RTB13 or P2-RTB13-1 removable terminal block.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-06TRS>

Technical Specifications

Brand	Productivity2000
Item	Output module
I/O Module Type	Relay
Number of Output Points	6
Nominal Output Voltage	5-30 VDC/5-264 VAC
Relay Configuration	(5) Form A (SPST) relays, (1) Form C (SPDT) relay
Number of Isolated Commons	6

Jumper Selectable Isolation	No
Number of Points per Common	1
Load Current	7A/point
Fuse Type	User-supplied external fuse
Requires	P2-RTB13 or P2-RTB13-1 removable terminal block
Programming Software	Productivity Suite programming software v4.2 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P2-06TRS.pdf>
See store item page for other formats.