

P2-08ADS-1 Cut Sheet



Productivity2000 analog input module, 8-channel, current, 16-bit, isolated, external 24 VDC required. Requires P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/P2-08ADS-1>

Technical Specifications

| | |
|-----------------------------------|------------------|
| Brand | Productivity2000 |
| Item | Input module |
| I/O Module Type | Analog |
| Number Of Input Channels | 8 |
| Input Signal Type(s) | Current |
| Analog Input Type | Sinking |
| Number of Isolated Commons | 4 |
| Isolated Channels | Yes |

| | |
|-----------------------------------|---|
| Input Resolution | 16-bit |
| Input Current Signal Range | 0–20 mA |
| Display Type | 4 x 10 character OLED display |
| External Power Requirement | 24 VDC |
| Requires | P2-RTB or P2-RTB-1 removable terminal block or ZIPLink pre-wired cables |
| Programming Software | Productivity Suite programming software v4.7 or later |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E139594 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/P2-08ADS-1.pdf>
See store item page for other formats.